

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

780nm CWL, 25mm Dia., OD 6 Ultra Narrow Filter



Ultra Narrow Bandpass Filters



Stock #36-641 3-4 DAYS

[Additional Bandwidths](#)

- 1 +

€1.492,00

ADD TO CART

Qty 1-9

€1.492,00

Qty 10+

€1.350,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
25.00

Angle of Incidence (°): 0
Optical Density OD (Average): 6.00
Clear Aperture CA (mm): 21.34
Center Wavelength CWL (nm): 780.00
Full Width-Half Max FWHM (nm): 1.20
Substrate: ☐ BOROFLOAT®
Minimum Transmission (%): >90
Coating: Hard Coated
Transmission (%): T _{abs} >90 @ 780nm
Type: Bandpass Filter
Blocking Wavelength Range (nm): 390 - 769, 791 - 1000
Construction: Mounted in Black Anodized Ring
Mount Thickness (mm): 5.0
Note: Filter Design: Multi-Cavity
Substrate Thickness (mm): 2.00

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant