

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

CO₂ Flat Top Beam Snaper 7 mm | πSnaper 7_7_10.6

See More by [AdiOptica](#)



Stock #34-259 3-4 DAYS



1



€6.484,00

ADD TO CART

Qty 1-4

€6.484,00

Qty 5+

€5.835,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Design Wavelength DWL (nm):
10600

Diameter (mm):
39.00

Entrance Beam Diameter, 1/e² (mm):
7

Model Number: πShaper 7_7_10.6
Length (mm): 143.00
Mounting Threads: M27 x 1
Type: Beam Shaper
Weight (g): <270
Wavelength Range (nm): 10000 - 11000
Style: Flat Top
Damage Threshold, By Design: ☐ 20 mJ/cm ² @ 5ns (typical)
Output Diameter, FWHM (mm): 7

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 240: Compliant