

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 850nm, 25.2 X 35.6mm High Performance Fluorescence Dichroic Filter



Stock #34-749 ☐ In Stock

-

1

+

 €465,00

ADD TO CART

Qty 1-5

€465,00

Qty 6+

€372,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Dimensions (mm):
25.2 x 35.6

Angle of Incidence (°):
45

Cut-On Wavelength (nm):
850.00

Substrate: Fused Silica (Coming 7980)
Length (mm): 35.60
Coating: Hard Coated
Reflection (%): R_{avg} >98%
Reflection Wavelength (nm): 635 - 805
Surface Quality: 40-20
Thickness (mm): 1.05 ±0.1
Transmission (%): T_{avg} >90%
Transmission Wavelength (nm): 857 - 1050
Type: Dichroic Filter
Width (mm): 25.20
Dimensional Tolerance (mm): +0.0/-0.2
Transmitted Wavefront, RMS: λ/10
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2
Wavelength Range (nm): 635 - 1050
Surface Flatness (P-V): λ/2

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant