


950nm, 6 x 6mm, OD 2.0 Shortpass Filter



OD 2.0 Shortpass Filters

Stock #15-244 3-4 DAYS

⊖ 1 ⊕ **€45,00**

ADD TO CART

Qty 1-9
€45,00
Qty 10+
€40,50
Volume Pricing
Request Quote

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads	
Dimensions (mm): 6.00 x 6.00 +0.00/-0.20	
Angle of Incidence (°): 0	
Optical Density OD (Average): ≥2.0	

Cut-Off Wavelength (nm): 950.00 ±19
Substrate: BOROFLOAT®
Length (mm): 6.00
Coating: Hard Coated
Rejection Wavelength (nm): 1025 - 1250
Surface Quality: 60-40
Thickness (mm): 2.00 ±0.10
Transmission (%): ≥85
Transmission Wavelength (nm): 500 - 900
Type: Shortpass Filter
Width (mm): 6.00
Clear Aperture (%): 90
Environmental Durability: ML-STD-810F, Section 507.4
Physical Durability: ML-C-48497A, Section 3.4.1
Wavelength Range (nm): 500 - 1250

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View