

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 980nm, 50mm Diameter, Raman Edge Filter



Stock #86-265 □ In Stock

- 1 + €2.035,00

ADD TO CART

Qty 1-9

€2.035,00

Qty 10+

€1.695,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Diameter (mm):
50.00 +0.0/-0.1

Angle of Incidence (°):
0 ±2

Optical Density OD (Average):
≥6.0

Cut-On Wavelength (nm): 989.80
Design Wavelength DWL (nm): 980
Substrate:  Fused Silica (Corning 7980)
Coating: Hard Coated
Rejection Wavelength (nm): 770 - 980
Surface Quality: 60-40
Thickness Tolerance (mm): +0.1/-0.1
Transmission (%): >93
Type: Longpass Filter
Transition Width (nm): <9.8
Clear Aperture (%): >80
Durability: Environmental: MIL-STD-810F Physical: MIL-C-48497A
Transmitted Wavefront, RMS: <λ/4 @ 633nm
Mount Thickness (mm): 3.5
Note: Bandwidth (nm): >1000
Coating Specification: T _{avg} ≥93% @ 992.7 - 2000nm
Wavelength Range (nm): 770 - 2000
Laser Blocking Wavelength (nm): 980.00

Regulatory Compliance

RoHS 2015: Compliant
Reach 209: Compliant
Certificate of Conformance: View