

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union


SUBMIT

Allied Vision Alvium 1800 U-040m, 1/2.9" 0.4MP S-Mount, USB 3.1 Monochrome Camera (Partial Housing)

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Partial Housing, S-Mbunt (Front)



Stock #14-853 [CONTACT US](#)

[Similar Cameras](#)

1 **€357,00**

ADD TO CART

Qty 1+

€357,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Alvium
Model Number: 1800 U-040m
Imaging Sensor: Sony IMX287
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/2.9"
Resolution (MegaPixels): 0.40
Pixels (H x V): 728 x 544
Pixel Size, H x V (µm): 6.9 x 6.9
Sensing Area, H x V (mm): 5.0 x 3.8
Frame Rate (fps): 281.00
Pixel Depth: 8/10/12 bit
Exposure Time: 177µs - 10s
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 1.9
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 25 x 29 x 29 (includes connectors and lens mount)
Weight (g): 45
Mount: M12 x 0.5 (S-Mount)
Housing: Partial
Interface Port Orientation: Back Panel
Dynamic Range (dB): 74
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant