

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Allied Vision Alvium USB 3.1 Cameras



Stock #19-607 3-4 DAYS

[Similar Cameras](#)



1



€2.163,00

ADD TO CART

Qty 1+

€2.163,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Avium
Model Number: 1800 U-2040m
Imaging Sensor: Sony IMX541
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 20.40
Pixels (H x V): 4,512 x 4,512
Pixel Size, H x V (µm): 2.74 x 2.74
Sensing Area, H x V (mm): 12.4 x 12.4
Frame Rate (fps): 17.00
Pixel Depth: 8/10/12 bit
Exposure Time: 164µs - 10s @ 450 MBps 161µs - 10s @ 200 MBps
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 3.9
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 38 x 29 x 29 (includes connectors and lens mount)
Weight (g): 65
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant