

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

Allied Vision Alvium 1800 U-500m, 1/2.5" 5.0MP C-Mount, USB 3.1 Monochrome Camera

See More by [Allied Vision](#)



Allied Vision Alvium Camera, Full Housing (Front)



Stock #14-126 3-4 DAYS

[Similar Cameras](#)



1



€315,00

ADD TO CART

Qty 1+

€315,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Video Output:

USB 3.1 Gen 1

Type:

Monochrome Camera

Manufacturer: Allied Vision
Mounting Threads: ¼-20 and M6 with Tripod Mount Adapter #14-156
Image Buffer: 256KB
Camera Family: Avium
Model Number: 1800 U-500m
Imaging Sensor: ON Semi AR0521
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Rolling
Camera Sensor Format: 1/2.5"
Resolution (MegaPixels): 5.00
Pixels (H x V): 2,592 x 1,944
Pixel Size, H x V (µm): 2.2 x 2.2
Sensing Area, H x V (mm): 5.7 x 4.3
Frame Rate (fps): 67.00
Pixel Depth: 8/10 bit
Exposure Time: 13µs - 849ms
Connector: USB 3.1 Gen 1, Micro-B
Power Supply: Power over USB or via GPIO
Power Consumption (W): 2.2
GPIOs: 4 Programmable TTL GPIOs
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 38 x 29 x 29 (includes connectors and lens mount)
Weight (g): 60
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 63
Operating Temperature (°C): -20 to +65 (housing temperature)
Storage Temperature (°C): -20 to +85
GPIO Connector Type: 7-pin JST
Machine Vision Standard: USB3 Vision v1.0, GenICam

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant