

[All Products](#) / [Cameras](#) / [Gigabit Ethernet Cameras](#) / [Allied Vision Manta GigE Cameras](#)

[See all 56 Products in Family](#)

# Allied Vision Manta G-033 1/2" Monochrome CCD Camera

See More by [Allied Vision](#)



Allied Vsion Manta GigE Cameras (Front)



Stock **#84-361** 3-4 DAYS

[Similar Cameras](#)



1



€876,00

ADD TO CART

Qty 1+

€876,00

Volume Pricing

[Request Quote](#)

 Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Video Output:**  
GigE

**Type:**  
Monochrome Camera

|                                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Manufacturer:</b><br>Allied Vision                                                                                                                                                                     |
| <b>Mounting Threads:</b><br>¼-20 with Tripod Mount Adapter <a href="#">#89-996</a>                                                                                                                        |
| <b>Image Buffer:</b><br>32MB                                                                                                                                                                              |
| <b>Camera Family:</b><br>Manta                                                                                                                                                                            |
| <b>Model Number:</b><br>Manta G-033B                                                                                                                                                                      |
| <b>Imaging Sensor:</b><br>Sony ICX414                                                                                                                                                                     |
| <b>Type of Sensor:</b><br>Progressive Scan CCD                                                                                                                                                            |
| <b>Type of Shutter:</b><br>Global                                                                                                                                                                         |
| <b>Camera Sensor Format:</b><br>1/2"                                                                                                                                                                      |
| <b>Resolution (MegaPixels):</b><br>0.30                                                                                                                                                                   |
| <b>Pixels (H x V):</b><br>656 x 492                                                                                                                                                                       |
| <b>Pixel Size, H x V (µm):</b><br>9.9 x 9.9                                                                                                                                                               |
| <b>Sensing Area, H x V (mm):</b><br>6.5 x 4.9                                                                                                                                                             |
| <b>Frame Rate (fps):</b><br>88.70                                                                                                                                                                         |
| <b>Pixel Depth:</b><br>12 bit                                                                                                                                                                             |
| <b>Exposure Time:</b><br>Via Software                                                                                                                                                                     |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                                                                                                                                          |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#15-281</a><br>Europe: <a href="#">#15-281</a><br>Japan: <a href="#">#15-281</a><br>China: <a href="#">#15-281</a> |
| <b>Power Consumption (W):</b><br>3.6 (12VDC External Power Supply)                                                                                                                                        |
| <b>GPIOs:</b><br>2 opto-isolated inputs, 2 opto-isolated outputs                                                                                                                                          |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO) or Software Trigger                                                                                                                                    |
| <b>Dimensions (mm):</b><br>71 x 44 x 29 (excludes connectors and lens mount)                                                                                                                              |
| <b>Weight (g):</b><br>200                                                                                                                                                                                 |
| <b>Mount:</b><br>C-Mount                                                                                                                                                                                  |
| <b>Housing:</b><br>Full                                                                                                                                                                                   |
| <b>Interface Port Orientation:</b><br>Back Panel                                                                                                                                                          |
| <b>Dynamic Range (dB):</b><br>61.5                                                                                                                                                                        |
| <b>Operating Temperature (°C):</b><br>+5 to +45                                                                                                                                                           |
| <b>Storage Temperature (°C):</b><br>-10 to +70                                                                                                                                                            |
| <b>GPIO Connector Type:</b><br>12-pin Hirose (HR10)                                                                                                                                                       |
| <b>Machine Vision Standard:</b><br>GigE Vision v1.2, GenICam SFNC V1.2.1                                                                                                                                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |

