

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

Basler ace2 a2A3840-45ucPRO Color USB3 Pro Camera



Basler ace2 USB 3.0 Cameras (Front)



Stock #16-634 3-4 DAYS

[Similar Cameras](#)



1



€469,00

ADD TO CART

Qty 1+

€469,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:  
USB 3.0

Type:  
Color Camera

Manufacturer:  
Basler

|                                                                                    |
|------------------------------------------------------------------------------------|
| <b>Mounting Threads:</b><br>¼-20 with Tripod Mount Adapter <a href="#">#16-641</a> |
| <b>Image Buffer:</b><br>Not Specified                                              |
| <b>Camera Family:</b><br>ace2                                                      |
| <b>Model Number:</b><br>a2A3840-45ucPRO                                            |
| <b>Imaging Sensor:</b><br>Sony IMX334                                              |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                    |
| <b>Type of Shutter:</b><br>Rolling                                                 |
| <b>Camera Sensor Format:</b><br>1/1.8"                                             |
| <b>Resolution (MegaPixels):</b><br>8.30                                            |
| <b>Pixels (H x V):</b><br>3,840 x 2,160                                            |
| <b>Pixel Size, H x V (µm):</b><br>2.00 x 2.00                                      |
| <b>Sensing Area, H x V (mm):</b><br>7.7 x 4.3                                      |
| <b>Frame Rate (fps):</b><br>45.00                                                  |
| <b>Pixel Depth:</b><br>8/10/12 bit                                                 |
| <b>Exposure Time:</b><br>Freely Programmable                                       |
| <b>Connector:</b><br>USB 3.0, Micro-B                                              |
| <b>Power Supply:</b><br>Power over USB                                             |
| <b>Power Consumption (W):</b><br>3.4                                               |
| <b>GPIOs:</b><br>1 opto-coupled input line, 2 general purpose I/O (GPIO) lines     |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or Free-Run  |
| <b>Dimensions (mm):</b><br>36.3 x 29 x 29 (excludes connectors and lens mount)     |
| <b>Weight (g):</b><br><90                                                          |
| <b>Mount:</b><br>C-Mount                                                           |
| <b>Housing:</b><br>Full                                                            |
| <b>Interface Port Orientation:</b><br>Back Panel                                   |
| <b>Dynamic Range (dB):</b><br>69.5                                                 |
| <b>Operating Temperature (°C):</b><br>-10 to +60                                   |
| <b>Storage Temperature (°C):</b><br>-20 to +80                                     |
| <b>GPIO Connector Type:</b><br>6-pin MB                                            |
| <b>Machine Vision Standard:</b><br>USB3 Vision v1.0, GenICam                       |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |