

## Basler ace acA1440-73gc Color GigE Camera



Basler ace GigE Cameras



Stock **#11-495** 3-4 DAYS

[Similar Cameras](#)

⊖ 1 ⊕

€429,00

ADD TO CART

Qty 1+

€429,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

**Video Output:**  
GigE (PoE)

**Type:**  
Color Camera

**Manufacturer:**  
Basler

|                                                                                                                                                                                                                                             |
|---------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Mounting Threads:</b><br>1/4-20 with Tripod Mount Adapter <a href="#">#88-517</a>                                                                                                                                                        |
| <b>Camera Family:</b><br>ace                                                                                                                                                                                                                |
| <b>Model Number:</b><br>acA1440-73gc                                                                                                                                                                                                        |
| <b>Imaging Sensor:</b><br>Sony IMX273                                                                                                                                                                                                       |
| <b>Type of Sensor:</b><br>Progressive Scan CMOS                                                                                                                                                                                             |
| <b>Type of Shutter:</b><br>Global                                                                                                                                                                                                           |
| <b>Camera Sensor Format:</b><br>1/2.9"                                                                                                                                                                                                      |
| <b>Resolution (MegaPixels):</b><br>1.60                                                                                                                                                                                                     |
| <b>Pixels (H x V):</b><br>1,440 x 1,080                                                                                                                                                                                                     |
| <b>Pixel Size, H x V (µm):</b><br>3.45 x 3.45                                                                                                                                                                                               |
| <b>Sensing Area, H x V (mm):</b><br>4.97 x 3.73                                                                                                                                                                                             |
| <b>Frame Rate (fps):</b><br>73.00                                                                                                                                                                                                           |
| <b>Pixel Depth:</b><br>10/12 bit                                                                                                                                                                                                            |
| <b>Exposure Time:</b><br>Freely Programmable                                                                                                                                                                                                |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                                                                                                                                                                            |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#68-466</a><br>Europe: <a href="#">#68-466</a><br>Japan: <a href="#">#68-466</a><br>Korea: <a href="#">#68-466</a><br>China: <a href="#">#68-466</a> |
| <b>Power Consumption (W):</b><br>2.9 (12VDC External Power Supply)<br>3.2 (PoE)                                                                                                                                                             |
| <b>GPIOs:</b><br>1 opto-coupled input line, 1 opto-coupled output line,<br>1 general purpose I/O (GPIO) line                                                                                                                                |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO), Software Trigger, or Free-Run                                                                                                                                                           |
| <b>Dimensions (mm):</b><br>42 x 29 x 29 (excludes connectors and lens mount)                                                                                                                                                                |
| <b>Weight (g):</b><br>90                                                                                                                                                                                                                    |
| <b>Mount:</b><br>C-Mount                                                                                                                                                                                                                    |
| <b>Housing:</b><br>Full                                                                                                                                                                                                                     |
| <b>Interface Port Orientation:</b><br>Back Panel                                                                                                                                                                                            |
| <b>Dynamic Range (dB):</b><br>Not Specified                                                                                                                                                                                                 |
| <b>Operating Temperature (°C):</b><br>0 to +50                                                                                                                                                                                              |
| <b>Storage Temperature (°C):</b><br>-20 to +80                                                                                                                                                                                              |
| <b>GPIO Connector Type:</b><br>6-pin Hirose (HR10)                                                                                                                                                                                          |
| <b>Machine Vision Standard:</b><br>GigE Vision, GenICam                                                                                                                                                                                     |
| <b>Operating System:</b><br>Software Driver: Windows, Linux - 32 and 64 bit                                                                                                                                                                 |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |

