

Basler ace acA720-290gm Monochrome GigE Camera



Basler ace GigE Cameras



Stock **#11-492** 3-4 DAYS

[Similar Cameras](#)

⊖ 1 ⊕

€379,00

ADD TO CART

Qty 1+

€379,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
GigE (PoE)

Type:
Monochrome Camera

Manufacturer:
Basler

Mounting Threads: 1/4-20 with Tripod Mount Adapter #88-517
Camera Family: ace
Model Number: acA720-290gm
Imaging Sensor: Sony IMX287
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1/2.9"
Resolution (MegaPixels): 0.40
Pixels (H x V): 720 x 540
Pixel Size, H x V (µm): 6.9 x 6.9
Sensing Area, H x V (mm): 4.97 x 3.73
Frame Rate (fps): 291.00
Pixel Depth: 10/12 bit
Exposure Time: Freely Programmable
Connector: GigE, RJ45 with Screw Locks
Power Supply: Power Supply Required and Sold Separately. USA: #68-466 Europe: #68-466 Japan: #68-466 Korea: #68-466 China: #68-466
Power Consumption (W): 2.9 (12VDC External Power Supply) 3.2 (PoE)
GPIOs: 1 opto-coupled input line, 1 opto-coupled output line, 1 general purpose I/O (GPIO) line
Synchronization: Hardware Trigger (GPIO), Software Trigger, or Free-Run
Dimensions (mm): 42 x 29 x 29 (excludes connectors and lens mount)
Weight (g): 90
Mount: C-Mount
Housing: Full
Interface Port Orientation: Back Panel
Dynamic Range (dB): 74.2
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -20 to +80
GPIO Connector Type: 6-pin Hirose (HR10)
Machine Vision Standard: GigE Vision, GenICam
Operating System: Software Driver: Windows, Linux - 32 and 64 bit

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant

