

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union



SUBMIT

Coarse/Fine Movement, 1/4-20 w/ Rotation, Rack & Pinion



#59-322

Stock #59-322 3-4 DAYS



1



€571,00

ADD TO CART

Qty 1+

€571,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):

Rack and Pinion Block: 50 H x30 W x50 L

Travel (mm):

35 (+23/-12) in Y

Type:

Rack and Pinion Mount

Travel Per Knob Rotation (mm):

25.5 coarse, 3.2 fine

Load Capacity (kg):

2.00
Note: 1/4-20 Stud
Type of Movement: Linear (Y), Rotation
Type of Adjustment: Coarse/Fine Movement
Optical Centerline from Post (mm): 51.00
Mounting Post Hole and Thread: 3/4" Diameter Post 1/4-20 Tapped Hole

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View
