

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® 65mm Sq, 15kg Load Capacity, 25mm Travel, Metric Dovetail Stage



#16-713: Dovetail Stage, 65mm SQ, English



Stock #16-716 3-4 DAYS

- 1 +

€180,00

ADD TO CART

Qty 1-9

€180,00

Qty 10+

€158,50

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Type of Movement:
Linear (X)

Guide System:
Dovetail

Type of Drive: Lead Screw
Drive Orientation: Center Drive
Type: Metric
Stage Size (mm): 65 x 65
Travel (mm): 25
Travel (inches): 0.98
Construction: Matte Black Finish Brass
Leadscrew Pitch (mm): 0.5
Load Capacity (kg): 15
Mounting Threads: (9) M6 x 1, (4) M3 x 0.5, (8) M2 x 0.4
Stage Size (inches): 2.56 x 2.56
Straight Line Accuracy (µm): 10
Included Hardware: 4X M6 x 1.0, 10mmL Socket Head Cap Screws; 1X 3mm Allen Wrench; 1X 2.5mm Allen Wrench

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View