

LS17 Adjustable Temples Wrap Around Frame, Laser Safety Glasses



Stock #12-746 ☐ In Stock

-

1

+

€370,00

ADD TO CART

Qty 1-5

€370,00

Qty 6+

€333,00

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Color:
Clear

Optical Density OD (Average):
>3 @ 850 - 2800nm
>4 @ 900 - 2600nm
>5 @ 950 - 1010nm

>7 @ 1010 - 1500nm
>5 @ 1500 - 2350nm
>5 @ 2800 - 10,600nm

Visible Light Transmission VLT (%):
75

EN 207/208 Ratings:
DIR LB3 + MLB3Y @ 850-900nm, DIR LB4 + MLB4Y @ 900-950nm, DIR LB5 + MLB5Y @ 950-1,000nm, DIR LB6 + MLB6Y @ 1,000-1,063nm, D LB6, IR LB7 + MLB7Y @ 1,063-1,400nm, DIR LB4 + MLB2 @ 1,400-1,600nm, DIR LB4 @ 1,600-2,200nm, DI LB4 @ 2,900-3,200nm + 9,000-11,000nm

Filter Material:
Glass

Filter:
LS17

Style:
Adjustable Temples Wrap Around

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)
