

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Olympus Plan Achromatic Objectives



Stock #16-879 3-4 DAYS



1



€680,00

ADD TO CART

Qty 1+

€680,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
11.00

Focal Length FL (mm):
90.00

Model Number: 1-U2B221
Length excluding Threads (mm): 39.10
Magnification: 2X
Maximum Diameter (mm): 24
Numerical Aperture NA: 0.06
Mounting Threads: RMS / 20.32mm x 36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 5.59
Depth of Field (µm): 76.39
Working Distance (mm): 5.8
Weight (g): 97.9
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 22
Parfocal Length (mm): 45
Immersion Liquid: N/A
Depth of Focus (µm): 306

Regulatory Compliance

Certificate of Conformance: View
--