

PL-D753CU-S-AFE-BL PixeLINK USB 3.0 Autofocus Color Camera



Pixelink® USB 3.0 Autofocus Liquid Lens Board Level Cameras

Stock **#14-176** [CONTACT US](#)

- 1 + **€1.695,00**

ADD TO CART

Qty 1+
€1.695,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Color Camera

Manufacturer:
Pixelink

Mounting Threads:
No Mounting Threads/Tripod Adapter

Image Buffer:

Not Specified
Camera Family: PL-D
Model Number: PL-D753CU-S-AFE-BL
Imaging Sensor: Sony IMX421
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 2/3"
Resolution (MegaPixels): 2.80
Pixels (H x V): 1,936 x 1,464
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 8.71 x 6.59
Frame Rate (fps): 141.00
Pixel Depth: 8/12 bit
Exposure Time: 10µs - 120s
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): Not Specified
GPIOs: 1 opto-isolated trigger input, 2 non-isolated outputs, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 50.8 x 35 x 13.36 (excludes lens mount)
Weight (g): 35.8
Mount: M12 x 0.5 (S-Mount)
Housing: Board Level
Interface Port Orientation: Side Panel
Dynamic Range (dB): 72
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -45 to +85
GPIO Connector Type: 8-pin Molex 1.25mm Pitch
Machine Vision Standard: USB3 Vision v1.0
Operating System: Software Driver: Windows 32 and 64 bit

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View