

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

PIXELINK PL-D757MU-BL, 1.1" 7.1MP, Board Level USB 3.0 Monochrome Camera



Pixelink® USB 3.0 Cameras (Board Level)



Stock #14-165 [CONTACT US](#)

[Similar Cameras](#)



1



€2.495,00

ADD TO CART

Qty 1+

€2.495,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Video Output:
USB 3.0

Type:
Monochrome Camera

Manufacturer:
Pixelink

Mounting Threads: 1/4-20 with Tripod Mount Adapter #26-179
Image Buffer: Not Specified
Camera Family: PL-D
Model Number: PL-D757MJ-BL
Imaging Sensor: Sony IMX420
Type of Sensor: Progressive Scan CMOS
Type of Shutter: Global
Camera Sensor Format: 1.1"
Resolution (MegaPixels): 7.10
Pixels (H x V): 3,208 x 2,200
Pixel Size, H x V (µm): 4.5 x 4.5
Sensing Area, H x V (mm): 14.44 x 9.9
Frame Rate (fps): 57.00
Pixel Depth: 8/12 bit
Exposure Time: 27µs - 120s
Connector: USB 3.0, Micro-B
Power Supply: Power over USB
Power Consumption (W): Not Specified
GPIOs: 1 non-isolated trigger input, 2 non-isolated outputs, 1 non-isolated input
Synchronization: Hardware Trigger (GPIO) or Software Trigger
Dimensions (mm): 50.8 x 35 x 13.36 (excludes lens mount)
Weight (g): 35.8
Mount: C-Mount
Housing: Board Level
Interface Port Orientation: Side Panel
Dynamic Range (dB): 72
Operating Temperature (°C): 0 to +50
Storage Temperature (°C): -45 to +85
GPIO Connector Type: 8-pin Molex 1.25mm Pitch
Machine Vision Standard: USB3 Vision v1.0
Operating System: Software Driver: Windows 32 and 64 bit

Regulatory Compliance

RoHS 2015: Compliant
Reach 224: Compliant
Certificate of Conformance: View