

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® 25mm ID Rotary Mount, 1/4-20



Rotary Mount, 1/4-20, #87-529

Stock #87-529 3-4 DAYS



1



€119,00

ADD TO CART

Qty 1+

€119,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Function:
Rotary

Type of Optics:
Circular/Cylindrical Tube

Plate Inner Diameter (mm):
25.0

Dimensions (mm):
50 Dia.

Bolt Circle Diameter for 6mm Dia. Thru (mm):

38.0
Bolt Circle Diameter for M3 Tapped (mm): 38.0
Thickness (mm): 21.0
Compatible Post: 1/4-20
Construction: Black Anodized Aluminum

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View