

# SCHOTT N-WG295, 12.5mm Dia., 1mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#16-404** 3-4 DAYS

- 1 + **€32,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-10                      |
| €32,00                        |
| Qty 11+                       |
| €28,00                        |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

## Get Product Downloads

**Diameter (mm):**  
12.50

**Cut-On Wavelength (nm):**  
295.00 ±6

|                                                        |
|--------------------------------------------------------|
| Density (g/cm³):<br>2.51                               |
| Glass/Filter Number:<br><a href="#">SCHOTT N-WG295</a> |
| Coating:<br>Uncoated                                   |
| Color:<br>Clear                                        |
| Passband Limit 1 $\lambda_{p1}$ (nm):<br>400           |
| Index of Refraction $n_d$ :<br>1.52                    |
| Spectral Transmittance $t_p$ (%):<br>99                |
| Stopband Limit $\lambda_s$ (nm):<br>250                |
| Surface Quality:<br>60-40                              |
| Transformation Temperature (°C):<br>565                |
| Thickness (mm):<br>1.00 ±0.1                           |
| Type:<br>Longpass Filter                               |
| Wavelength:<br>UV                                      |
| Dimensional Tolerance (mm):<br>±0.2                    |
| Reflection Factor $P_d$ :<br>0.92                      |
| Bevel:<br>Protective as needed                         |

## Regulatory Compliance

|                                                     |
|-----------------------------------------------------|
| Certificate of Conformance:<br><a href="#">View</a> |
|-----------------------------------------------------|