

SCHOTT NG4, 0.6 OD, 50mm Sq., Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-046** ☐ In Stock

-

1

+

€93,00

ADD TO CART

Qty 1-10

€93,00

Qty 11+

€82,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
0.6 ±0.03 @ 546nm

Glass/Filter Number:
[SCHOTT NG4](#)

Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 483
Thickness (mm): 1.10
Thickness Tolerance (mm): (nominal)
Transmission (%): 25.12 ±1.51% @ 546nm
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Wavelength Range (nm): 400 - 700

Regulatory Compliance

RoHS: Compliant
Reach 224: Compliant
Certificate of Conformance: View