

SCHOTT NG9, 25mm Dia., 1mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-099** ☐ In Stock

-

1

+

€42,00

ADD TO CART

Qty 1-10
€42,00
Qty 11+
€37,00
Volume Pricing
Request Quote
! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
1.42

Glass/Filter Number: SCHOTT NG9
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 470
Thickness (mm): 1.00 ±0.1
Transmission (%): 3.8
Transmission Tolerance (%): (nominal)
Type: Neutral Density Filter
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Optical Density Tolerance (%): (nominal)

Regulatory Compliance

RoHS: Compliant
Reach 223: Compliant
Certificate of Conformance: View
