



SCHOTT NG9, 50mm Sq., 3mm Thick, Absorptive ND Filter

See More by [SCHOTT Optical Components](#)



SCHOTT NG Gray Glass Neutral Density (ND) Filters



Stock **#14-102** ☐ In Stock

-

1

+

€93,00

ADD TO CART

Qty 1-10
€93,00

Qty 11+
€82,00

Volume Pricing
Request Quote

 Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Optical Density OD (Average):
4.18

Glass/Filter Number: SCHOTT NG9
Length (mm): 50.00
Coating: Uncoated
Index of Refraction n_d: 1.51
Surface Quality: 60-40
Transformation Temperature (°C): 470
Thickness (mm): 3.00 ±0.2
Transmission (%): 0.007
Transmission Tolerance (%): (nominal)
Type: Neutral Density Filter
Width (mm): 50.00
Parallelism (arcmin): ≤3
Dimensional Tolerance (mm): ±0.2
Optical Density Tolerance (%): (nominal)

Regulatory Compliance

RoHS: Compliant
Reach 223: Compliant
Certificate of Conformance: View