


SCHOTT OG530, 50mm Sq., 2mm Thick, Colored Glass Longpass Filter

See More by [SCHOTT Optical Components](#)



Stock **#14-497** ☐ In Stock

-

1

+

€77,50

ADD TO CART

Qty 1-10
€77,50
Qty 11+
€76,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
50.0 x 50.0

Cut-On Wavelength (nm):
530.00 ±6

Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG530
Length (mm): 50.00
Coating: Uncoated
Color: Yellow
Passband Limit 1 λ_{p1} (nm): 600
Index of Refraction n_d: 1.51
Spectral Transmittance t_p (%): 93
Stopband Limit λ_s(nm): 460
Surface Quality: 60-40
Transformation Temperature (°C): 506
Thickness (mm): 2.00 ±0.2
Type: Longpass Filter
Wavelength: VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.92
Bevel: Protective as needed

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Compliant