

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock **#16-416** [CONTACT US](#)



1



€32,00

ADD TO CART

Qty 1-10

€32,00

Qty 11+

€28,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Cut-On Wavelength (nm):
550.00 ±6

Density (g/cm³): 2.56
Glass/Filter Number: SCHOTT OG550
Coating: Uncoated
Color: Orange
Passband Limit 1 λ_{p1} (nm): 620
Index of Refraction n_d : 1.51
Spectral Transmittance t_p (%): 93
Stopband Limit λ_s (nm): 480
Surface Quality: 60-40
Transformation Temperature (°C): 507
Thickness (mm): 1.00 ±0.1
Type: Longpass Filter
Wavelength: VIS
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d : 0.92
Bevel: Protective as needed

Regulatory Compliance

Certificate of Conformance: View
