

# Allied Vision Prosilica GT1380 2/3" Color CCD Camera

See More by [Allied Vision](#)



Stock **#87-070** [CONTACT US](#)

[Similar Cameras](#)



1



€2.826,00

ADD TO CART

Qty 1+

€2.826,00

Volume Pricing

[Request Quote](#)

**!** Prices shown are exclusive of VAT/local taxes

**Note:** This item requires accessories for use | [Learn More](#)

Get Product Downloads

**Video Output:**  
GigE (PoE)

**Type:**  
Color Camera

**Manufacturer:**  
Allied Vision

**Mounting Threads:**  
1/4-20 with Tripod Mount Adapter [#87-412](#)

|                                                                                                                                                                                                           |
|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| <b>Image Buffer:</b><br>128MB                                                                                                                                                                             |
| <b>Camera Family:</b><br>Prosilica GT                                                                                                                                                                     |
| <b>Model Number:</b><br>GT 1380 C                                                                                                                                                                         |
| <b>Imaging Sensor:</b><br>Sony ICX285                                                                                                                                                                     |
| <b>Type of Sensor:</b><br>Progressive Scan CCD                                                                                                                                                            |
| <b>Type of Shutter:</b><br>Global                                                                                                                                                                         |
| <b>Camera Sensor Format:</b><br>2/3"                                                                                                                                                                      |
| <b>Resolution (MegaPixels):</b><br>1.40                                                                                                                                                                   |
| <b>Pixels (H x V):</b><br>1,360 x 1,024                                                                                                                                                                   |
| <b>Pixel Size, H x V (µm):</b><br>6.45 x 6.45                                                                                                                                                             |
| <b>Sensing Area, H x V (mm):</b><br>8.77 x 6.6                                                                                                                                                            |
| <b>Frame Rate (fps):</b><br>30.00                                                                                                                                                                         |
| <b>Pixel Depth:</b><br>8/14 bit                                                                                                                                                                           |
| <b>Exposure Time:</b><br>10µs - 60s                                                                                                                                                                       |
| <b>Connector:</b><br>GigE, RJ45 with Screw Locks                                                                                                                                                          |
| <b>Power Supply:</b><br>Power Supply Required and Sold Separately.<br>USA: <a href="#">#15-281</a><br>Europe: <a href="#">#15-281</a><br>Japan: <a href="#">#15-281</a><br>China: <a href="#">#15-281</a> |
| <b>Power Consumption (W):</b><br>3.4 (12VDC External Power Supply)<br>4.2 (PoE)                                                                                                                           |
| <b>GPIOs:</b><br>1 opto-isolated input, 2 opto-isolated outputs, 1 non-isolated input, 2 non-isolated outputs                                                                                             |
| <b>Synchronization:</b><br>Hardware Trigger (GPIO) or Software Trigger                                                                                                                                    |
| <b>Dimensions (mm):</b><br>70.5 x 53.3 x 33 (excludes connectors and lens mount)                                                                                                                          |
| <b>Weight (g):</b><br>211                                                                                                                                                                                 |
| <b>Mount:</b><br>C-Mount                                                                                                                                                                                  |
| <b>Housing:</b><br>Full                                                                                                                                                                                   |
| <b>Interface Port Orientation:</b><br>Back Panel                                                                                                                                                          |
| <b>Dynamic Range (dB):</b><br>60.9                                                                                                                                                                        |
| <b>Operating Temperature (°C):</b><br>-20 to +65                                                                                                                                                          |
| <b>Storage Temperature (°C):</b><br>-20 to +70                                                                                                                                                            |
| <b>GPIO Connector Type:</b><br>12-pin Hirose (HR10)                                                                                                                                                       |
| <b>Machine Vision Standard:</b><br>GigE Vision V1.2, GenICam SFNC V1.2.1                                                                                                                                  |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |