

TECHSPEC® Blue M25.5 x 0.50 High Performance Machine Vision Filter



TECHSPEC® High Performance Mounted Machine Vision Filters

Stock **#89-764** ☒ In Stock



1



€166,00

ADD TO CART

Qty 1-9

€166,00

Qty 10+

€153,30

Volume Pricing

[Request Quote](#)

⚠ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Blocking Wavelength Range (nm):
200-400, 550-1200

Clear Aperture CA (mm):
21.5

Coating:
Hard Coated

Filter Thread: M25.5 x0.50
Color: Blue
Center Wavelength CWL (nm): 470.00
Construction: Mounted in Black Anodized Ring
Full Width-Half Max FWHM (nm): 85.00
Mount Thickness (mm): 4.5
Mount Thickness Including Threads (mm): 6.5
Note: OD ≥3.0 @ 550 - 1200nm OD ≥4.0 @ 200 - 400nm
Optical Density OD (Average): ≥3.0
Outer Diameter (mm): 27.5
Substrate Thickness (mm): 1.75 ±0.10
Type: Mounted Imaging Filter
Average Transmission (%): ≥90
Environmental Durability: Humidity per MIL-STD-810H, Section 507.6 Temperature per MIL-STD-810H, Section 501.7 and 502.7
Physical Durability: Adhesion per MIL-PRF-13830B, Section C.4.5.12 Moderate abrasion per MIL-PRF-13830B, Section C.4.5.11 Cleaning per MIL-C-48497A Section 4.5.4.2

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View