

TECHSPEC® C-Mount Achromat Pair 1:1 with 100 and 100mm Focal Lengths



Stock **#87-192** ☐ In Stock

⊖ 1 ⊕ **€370,00**

ADD TO CART

Qty 1-5
€370,00
Qty 6+
€296,00
Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
40-20

Working f#:
f/5.0 - f/125

Coating:
VIS 0° (425-675nm)

Coating Specification:

R _{avg} ≤0.4% @ 425 - 675nm
Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 100.0
Effective Focal Length EFL B (mm): 100.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:1
Object Distance (mm): 85.00
Image Distance (mm): 85.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View