

TECHSPEC® C-Mount Achromat Pair 1:2 with 30 and 60mm Focal Lengths



Stock **#87-186** 3-4 DAYS

⊖ 1 ⊕ **€370,00**

ADD TO CART

Qty 1-5
€370,00

Qty 6+
€296,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
40-20

Working f#:
f/2.8 - f/76

Coating:
VIS 0° (425-675nm)

Coating Specification:

R _{avg} ≤0.4% @ 425 - 675nm
Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 30.0
Effective Focal Length EFL B (mm): 60.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:2
Object Distance (mm): 15.00
Image Distance (mm): 40.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View