

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® C-Mount Achromat Pair 1:2 with 50 and 100mm Focal Lengths



Stock #87-189 [CONTACT US](#)



1



€370,00

ADD TO CART

Qty 1-5

€370,00

Qty 6+

€296,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Surface Quality:
40-20

Working f#:
f/5.0 - f/125

Coating:
VIS 0° (425-675nm)

Coating Specification:

R _{avg} ≤0.4% @ 425 - 675nm
Aperture (mm): 0.8 - 20
Effective Focal Length EFL A (mm): 50.0
Effective Focal Length EFL B (mm): 100.0
Housing Diameter (mm): 38.00
Housing Length (mm): 45.9
Magnification: 1:2
Object Distance (mm): 35.00
Image Distance (mm): 85.00
Type: Relay Lens
Wavelength Range (nm): 425 - 675

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View