

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

TECHSPEC® Elliptical Mirror 26.97 mm Minor Axis Enhanced Aluminum



Stock #32-132 3-4 DAYS

1 €93,00

ADD TO CART

Qty 1-5
€93,00
Qty 6+
€74,50
Volume Pricing
Request Quote

Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Minor Axis (mm):
26.97

Major Axis (mm):
38.15

Surface Flatness (P-V):
λ/8

Substrate: BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R_{avg} >95% @450 - 650nm
Coating: Enhanced Aluminum (450-650nm)
Coating Type: Metal
Clear Aperture CA (mm): 24.28 (Minor Axis) 34.34 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 6.35
Thickness Tolerance (inches): ±0.030
Thickness Tolerance (mm): ±0.76
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 0.65
Wavelength Range (nm): 450 - 650
Damage Threshold, Reference: 0.2 J/cm² @ 532nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant