

TECHSPEC® Elliptical Mirror 47.63mm Minor Axis Protected Silver



Stock **#89-459** 3-4 DAYS

- 1 + **€199,00**

ADD TO CART

Qty 1-5
€199,00

Qty 6+
€159,00

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Minor Axis (mm): 47.63
Major Axis (mm): 67.36
Surface Flatness (P-V): λ/8

Substrate: ☐ BOROFLOAT®
Surface Quality: 60-40
Dimensional Tolerance (mm): ±0.38
Dimensional Tolerance (inches): ±0.015
Coating Specification: R_{avg} >98% @450 - 2000nm R_{avg} >98% @2000 - 10,000nm
Coating: Protected Silver (450-10000nm)
Coating Type: Metal
Clear Aperture CA (mm): 42.88 (Minor Axis) 60.63 (Major Axis)
Note: Flatness specification is Peak to Valley
Thickness (mm): 11.68
Thickness Tolerance (inches): ±0.040
Thickness Tolerance (mm): ±1.02
Type: Flat Mirror
Wavelength Range (µm): 0.45 - 10
Wavelength Range (nm): 450 - 10000
Damage Threshold, Reference: ☐ 0.5 J/cm² @532nm & 1064nm, 10ns

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 233: Compliant