

**TECHSPEC® Elliptical Mirror 57.15mm Minor Axis Uncoated**



Stock **#32-098** 3-4 DAYS

⊖ 1 ⊕ **€276,00**

ADD TO CART

|                               |
|-------------------------------|
| Qty 1-5                       |
| €276,00                       |
| Qty 6+                        |
| €221,00                       |
| Volume Pricing                |
| <a href="#">Request Quote</a> |

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads



Minor Axis (mm):  
57.15

Major Axis (mm):  
80.82

Surface Flatness (P-V):  
λ/8

|                                                                            |
|----------------------------------------------------------------------------|
| <b>Substrate:</b> <input type="checkbox"/><br><a href="#">BOROFLOAT®</a>   |
| <b>Surface Quality:</b><br>60-40                                           |
| <b>Dimensional Tolerance (mm):</b><br>±0.79                                |
| <b>Dimensional Tolerance (inches):</b><br>±0.031                           |
| <b>Coating:</b><br>Uncoated                                                |
| <b>Coating Type:</b><br>Uncoated                                           |
| <b>Clear Aperture CA (mm):</b><br>51.44 (Minor Axis)<br>72.75 (Major Axis) |
| <b>Note:</b><br>Flatness specification is Peak to Valley                   |
| <b>Thickness (mm):</b><br>15.88                                            |
| <b>Thickness Tolerance (inches):</b><br>±0.060                             |
| <b>Thickness Tolerance (mm):</b><br>±1.52                                  |
| <b>Type:</b><br>Flat Mirror                                                |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |
| <b>Reach 235:</b><br><a href="#">Compliant</a>             |