

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

G Plan Apo 20X Objective

See More by [Mitutoyo](#)



Stock #58-175 3-4 DAYS

- 1 + €4.465,00

ADD TO CART

Qty 1+

€4.465,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
3.5

Horizontal Field of View, 1/2" Sensor:
0.32mm

Horizontal Field of View, 2/3" Sensor:
0.44mm

Focal Length FL (mm):
10.00

Model Number:

378-847
Length excluding Threads (mm): 65.60
Magnification: 20X
Maximum Diameter (mm): 34
Maximum Sensor Format: 2/3"
Numerical Aperture NA: 0.28
Mounting Threads: M26 x36 TPI
Compatible Tube Lens Focal Length (mm): Focal Length: 200mm
Type: Microscope Objective
Resolving Power (µm): 1.0
Depth of Field (µm): 3.50
Field of View, 24 Diameter Field Eyepiece (mm): 1.20
Operating Temperature (°C): +5 to +40
Operating Humidity: 20 - 80%
Working Distance (mm): 29.42 (30.60 through compatible cover glass)
Weight (g): 270.00
Wavelength Range (nm): 436 - 656
Style: Infinity Corrected
Manufacturer: Mitutoyo
Parfocal Length (mm): 96.19
Immersion Liquid: N/A

Regulatory Compliance

RoHS 2015: Exempt
Certificate of Conformance: View
Reach 240: Contains SVHC(s)