

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® IR (1150-1550nm) OD 4.0 25nm Bandpass Filter Kit, 50mm Dia



Stock #88-309 [CONTACT US](#)

- 1 + €4.996,00

ADD TO CART

Qty 1+

€4.996,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
50.00

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
25.00

Filters Included :
CWL: [1150nm](#), [1200nm](#), [1250nm](#), [1300nm](#), [1350nm](#),
[1400nm](#), [1450nm](#), [1500nm](#), [1550nm](#)

Coating:

Hard Coated
Type: Bandpass Filter
Typical Applications: LED Cleanup, Bio-Imaging, Machine Vision
Wavelength: IR
Number of Filters: 9
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.13

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View