

Coherent® EnergyMax 1191441 | 50μJ - 50mJ, USB

See More by [Coherent®](#)



Coherent® EnergyMax Laser Energy Sensors

Stock **#88-424** [CONTACT US](#)

- 1 + **€2.880,00**

ADD TO CART

Qty 1+

€2.880,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):
25

Connector:
USB

Model Number:
J-25MB-LE
Coherent Part Number: 1191441

Type:
Meterless

Type of Sensor: Pyroelectric
Length of Cable (m): 3.0
Linearity (%): ±3
Calibration Uncertainty (%): ±2
Calibration Wavelength (nm): 1064
Noise Equivalent Energy (μJ): <5
Maximum Repetition Rate (pps): 1000
Maximum Incident Beam Power (W): 5
Maximum Pulse Width (μs): 17
Wavelength Range (nm): 190 - 12000
Maximum Incident Energy Density: 500mJ/cm ² (10ns, 1064nm)
Energy Range: 50μJ - 50mJ

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View