

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Laser Detection Card NIR, #36-743

Stock #36-743 ☒ In Stock



1



€120,00

ADD TO CART

Qty 1+

€120,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):
86 x 54

Type:
Card

Wavelength:
NIR

Size of Active Area (mm):
42 x 23

Typical Applications:

Nd:YAG, Fiber Laser
Persistence (Stimulation Removed): <50 ms
Emission Color: Orange/Red (655nm)
Stimulation Range: 700 - 1400nm
Minimum Stimulation, Continuous: 8 μ W/cm ² @ 1064nm
Maximum Stimulation, Continuous: 100 W/cm ² @ 1064nm (estimated)
Maximum Stimulation, Single Pulse: 35 MW/cm ² @ 1064nm, 7ns (estimated)

Regulatory Compliance

Reach 191: Compliant
RoHS 2015: Compliant
Certificate of Conformance: View