

M22.5 x 0.50 Machine Vision Mounted Linear Glass Polarizing Filter



Stock #21-545 3-4 DAYS

⊖ 1 ⊕ **€64,50**

ADD TO CART

Qty 1-9
€64,50

Qty 10+
€61,50

Volume Pricing
Request Quote

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Clear Aperture CA (mm):
18.50

Coating:
Hardcoated

Diameter (mm):
24.00

Extinction Ratio:

up to 3000:1 @~600nm (nominal)
Filter Thread: M22.5 x 0.50
Surface Quality: 40-20
Type: Mounted Imaging Filter
Construction: Black Anodized Aluminum
Wavelength Range (nm): 400 - 700
Mount Thickness Including Threads (mm): 9.1

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View