

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

TECHSPEC® NIR (750-1100nm) OD 4.0 25nm Bandpass Filter Kit, 12.5mm Dia



Stock #88-294 3-4 DAYS



1



€915,00

ADD TO CART

Qty 1+

€915,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
12.50

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
25.00

Filters Included :
CWL: [750nm](#), [800nm](#), [850nm](#), [900nm](#), [950nm](#),
[1000nm](#), [1050nm](#), [1100nm](#)

Coating:

Hard Coated
Type: Bandpass Filter
Typical Applications: LED Cleanup, Bio-Imaging, Machine Vision
Wavelength: NIR
Number of Filters: 8
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.8

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View