

TECHSPEC® NIR (750-1100nm) OD 4.0 50nm Bandpass Filter Kit, 25mm Dia



Stock **#88-304** 3-4 DAYS

- 1 + **€1.599,00**

ADD TO CART

Qty 1+
€1.599,00

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Diameter (mm):
25.00

Optical Density OD (Average):
≥4.0

Full Width-Half Max FWHM (nm):
50.00

Filters Included :
CWL: [750nm](#), [800nm](#), [850nm](#), [900nm](#), [950nm](#),
[1000nm](#), [1050m](#), [1100nm](#)

Coating:

Hard Coated
Type: Bandpass Filter
Typical Applications: Bio-Imaging, Fluorescence Microscopy, Machine Vision
Wavelength: NIR
Number of Filters: 8
Environmental Durability: Humidity: MIL-STD 810.F, Method 507.4
Physical Durability: Adhesion: MIL-C-48497A, 3.4.1.1 Abrasion: MIL-C-48497A, 3.4.1.3 Temperature: MIL-C-48497A, 3.4.2.1 Cleaning: MIL-C-48497A, 3.4.2.18

Regulatory Compliance

RoHS: Not Compliant
Certificate of Conformance: View