

In order to provide more accurate inventory information, please select your shipping country:

Select Your Country/Region: European Union

SUBMIT

Coherent® OBIS™ 1261777 | 532nm LS 20mW Laser

See More by [Coherent®](#)



Stock #33-350 3-4 DAYS



1



€5.330,00

ADD TO CART

Qty 1+

€5.330,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads



Operating Temperature (°C):
15 to 40

Output Power (mW):
20

Polarization:

100:1
Power Stability (%): <2
Spatial Mode: TEM ₀₀
Wavelength (nm): 532.00 ±2
Mode Quality, M²: ≤1.1
Power Supply: Power Supply Required and Sold Separately. USA: #87-473 Europe: #87-473 Japan: #87-473 Korea: #87-473 China: #87-473
Warm-Up Time (minutes): <5
Pointing Stability (μrad/°C): <5
Modulation Frequency (MHz): Max Digital: 0.05
Modulation Frequency (kHz): 500 Max Analag
Beam Diameter Tolerance (mm): ±0.05
Pointing Stability (μrad): <30
RMS Noise: ≤0.25% (20Hz to 20MHz)
Beam Diameter (mm): 0.7
Manufacturer: Coherent®
Output Type: Free Space
Type of Laser: Diode
Beam Divergence (mrad): <1.2
Laser Class - CDRH: IIIb
Color: Green
Model Number: 1261777

Regulatory Compliance

RoHS 2015: Exempt
Reach 224: Contains SVHC(s)
Certificate of Conformance: View