

Olympus SLMPLN 100X Objective

See More by [Olympus](#)



#86-826

Stock **#86-826** [CONTACT US](#)

-

1

+

€6.913,00

ADD TO CART

Qty 1+

€6.913,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
0.26

Focal Length FL (mm):
1.80

Model Number:
1-U2M275

Length excluding Threads (mm): 37.40
Magnification: 100X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.60
Mounting Threads: RMS / 20.32mm x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.56
Depth of Field (µm): 0.76
Working Distance (mm): 7.6
Weight (g): 100
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--