

Olympus SLMPLN 20X Objective

See More by [Olympus](#)



#86-824

Stock **#86-824** 3-4 DAYS

- 1 + **€2.986,00**

ADD TO CART

Qty 1+
€2.986,00

Volume Pricing
Request Quote

! Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
1.3

Focal Length FL (mm):
9.00

Model Number:
1-U2M265

Length excluding Threads (mm): 20.00
Magnification: 20X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.25
Mounting Threads: RMS / 20.32mm x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 1.34
Depth of Field (µm): 4.40
Working Distance (mm): 25.0
Weight (g): 56
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--