

Olympus SLMPLN 50X Objective

See More by [Olympus](#)



#86-826



Stock #86-825 3-4 DAYS



1



€3.792,00

ADD TO CART

Qty 1+

€3.792,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Compatible Cover Glass Thickness (mm):
N/A

Field of View (mm):
0.53

Focal Length FL (mm):
3.60

Model Number: 1-U2M270
Length excluding Threads (mm): 27.00
Magnification: 50X
Maximum Diameter (mm): 26
Numerical Aperture NA: 0.35
Mounting Threads: RMS / 20.32mm x 36 TPI
Transmission (%): T> 90 from 400-700nm
Compatible Tube Lens Focal Length (mm): Focal Length: 180mm
Type: Microscope Objective
Resolving Power (µm): 0.96
Depth of Field (µm): 2.24
Working Distance (mm): 18.0
Weight (g): 74
Wavelength Range (nm): 400 - 700
Style: Infinity Corrected
Manufacturer: Olympus
Field Number (mm): 26.5
Parfocal Length (mm): 45
Immersion Liquid: N/A

Regulatory Compliance

Certificate of Conformance: View
--