

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

Coherent® Thermopile Power Sensor 1098412 | 150W, DB25

See More by [Coherent®](#)



Stock #88-415 3-4 DAYS

-

1

+

€1.525,00

ADD TO CART

Qty 1+

€1.525,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Active Area Diameter (mm):

50

Model Number:

PM150-50C

Coherent Part Number: 1098412

Type:

[Meter required](#)

Type of Sensor: Thermopile
Length of Cable (m): 2.0
Computer Interface: DB25
Calibration Uncertainty (%): ±1
Calibration Wavelength (nm): 514
Long Pulse Joule Mode Range (J): 1 - 150
Maximum Intermittent Power, <5min (W): 80 (air-cooled)
Cooling Method: Water/Air
Maximum Incident Power Density (kW/cm²): 6
Power Range: 300mW - 150W
Maximum Incident Energy Density (J/cm²): 0.6 @ 1064nm, 10ns
Compatible Meters: #35-203 , #12-393 , #59-978 , #88-411 , #66-277 , #88-412
Wavelength Range (nm): 250 - 11000
Wavelength Range (µm): 0.25 - 11

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View