

Red, 0.315" LED Spot Light

See More by [Advanced Illumination](#)



Stock #87-544 [CONTACT US](#)

1 **€192,00**

ADD TO CART

Qty 1+

€192,00

Volume Pricing

[Request Quote](#)

! Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Color:
Red

Diameter (mm):
7.90

Fiber Bundle Diameter (inches):
¼

Model Number:
SL-4301A-660-IC

Length (mm):
38.10

Outer Diameter (inches):
0.312

Wavelength (nm):
660.00

LED Lifetime (hours):
50,000

Power Supply:
Power Supply Required and Sold Separately.
USA: [#66-855](#)
Europe: [#66-855](#)
Japan: [#66-855](#)
Korea: [#33-773](#)
China: [#66-855](#)

Length of Cable (m):
1.5

Type of Illumination:
LED Illuminator

Manufacturer:
Advanced Illumination

Geometry:
Spot Light

Illumination Mode:
Constant

Regulatory Compliance

RoHS 2015:
[Compliant](#)

Certificate of Conformance:
[View](#)

Reach 233:
[Contains SVHC\(s\)](#)
