

Rodagon 50mm FL - Video Lens



Lens + Modular Focus Tube + Basler Line Scan Camera

Stock **#14-700** [CONTACT US](#)

⊖ 1 ⊕

€520,00

ADD TO CART

Qty 1+

€520,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Note: This item requires accessories for use | [Learn More](#)

Get Product Downloads

Field of View @ Min Working Distance (mm):
17.3

Iris Option:
Variable

Length (mm):
43.50

Horizontal Field of View, 1/2" Sensor:
6.8°

Filter Thread: M40.5 x 0.50
Maximum Diameter (mm): 50.0
Maximum Image Circle (mm): 40.00
Note: Requires Leica Lens Adapter M39 x 1/26" #14-705 , Modular Focus Tube #14-707 , and a lens mount adapter (C-Mount , F-Mount , T-Mount , SLR , or M72)
Type: Fixed Focal Length Lens
Focal Length FL (mm): 50.00
Primary Magnification PMAG: 0.37X
Maximum Sensor Format: 40mm (Image Circle)
Working Distance (mm): 155 - ∞
Mount: Adapter Required
Aperture (f/#): f/2.8 - f/16
Lens Wavelength Range: VIS

Regulatory Compliance

RoHS 2015: Compliant
Certificate of Conformance: View
Reach 235: Compliant