

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT

See More by [SCHOTT Optical Components](#)



Stock **#14-435** □ In Stock



1



€180,00

ADD TO CART

Qty 1-10

€180,00

Qty 11+

€159,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):

50.0 x 50.0

Center Wavelength CWL (nm):

500.00

Density (g/cm³): 2.85
Glass/Filter Number: SCHOTT BG62
Length (mm): 50.00
Coating: Uncoated
Color: Blue-Green
Index of Refraction n_d: 1.54
Surface Quality: 60-40
Transformation Temperature (°C): 410
Thickness (mm): 1.00 ±0.1
Type: IR Cut-Off Filter
Wavelength: UV-VIS
Width (mm): 50.00
Dimensional Tolerance (mm): ±0.2
Reflection Factor P_d: 0.91
Bevel: Protective as needed

Regulatory Compliance

RoHS: Compliant
Certificate of Conformance: View