

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union

SUBMIT

See More by [SCHOTT Optical Components](#)



Stock #14-437 □ In Stock



1



€180,00

ADD TO CART

Qty 1-10

€180,00

Qty 11+

€159,00

Volume Pricing

[Request Quote](#)

ⓘ Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):

50.0 x 50.0

Center Wavelength CWL (nm):

480.00

|                                                            |
|------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.79                            |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT BG63</a> |
| <b>Length (mm):</b><br>50.00                               |
| <b>Coating:</b><br>Uncoated                                |
| <b>Color:</b><br>Blue-Green                                |
| <b>Index of Refraction n<sub>d</sub>:</b><br>NA            |
| <b>Surface Quality:</b><br>60-40                           |
| <b>Transformation Temperature (°C):</b><br>416             |
| <b>Thickness (mm):</b><br>1.00 ±0.1                        |
| <b>Type:</b><br>IR Cut-Off Filter                          |
| <b>Wavelength:</b><br>UV-VIS                               |
| <b>Width (mm):</b><br>50.00                                |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                 |
| <b>Reflection Factor P<sub>d</sub>:</b><br>0.92            |
| <b>Bevel:</b><br>Protective as needed                      |

## Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS:</b><br><a href="#">Compliant</a>                  |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |