

In order to provide more accurate inventory information, please select your shipping country.

Select Your Country/Region: European Union



SUBMIT



Stock #14-465 ☐ In Stock



1



€77,50

ADD TO CART

Qty 1-10

€77,50

Qty 11+

€76,00

Volume Pricing

[Request Quote](#)

Prices shown are exclusive of VAT/local taxes

Get Product Downloads

Dimensions (mm):  
50.0 x 50.0

Cut-On Wavelength (nm):  
295.00 ±6

|                                                                |
|----------------------------------------------------------------|
| <b>Density (g/cm³):</b><br>2.51                                |
| <b>Glass/Filter Number:</b><br><a href="#">SCHOTT N-WG295</a>  |
| <b>Length (mm):</b><br>50.00                                   |
| <b>Coating:</b><br>Uncoated                                    |
| <b>Color:</b><br>Clear                                         |
| <b>Passband Limit 1 <math>\lambda_{p1}</math> (nm):</b><br>400 |
| <b>Index of Refraction <math>n_d</math>:</b><br>1.52           |
| <b>Spectral Transmittance <math>t_p</math> (%):</b><br>99      |
| <b>Stopband Limit <math>\lambda_s</math>(nm):</b><br>250       |
| <b>Surface Quality:</b><br>60-40                               |
| <b>Transformation Temperature (°C):</b><br>565                 |
| <b>Thickness (mm):</b><br>3.00 ±0.2                            |
| <b>Type:</b><br>Longpass Filter                                |
| <b>Wavelength:</b><br>UV                                       |
| <b>Width (mm):</b><br>50.00                                    |
| <b>Dimensional Tolerance (mm):</b><br>±0.2                     |
| <b>Reflection Factor <math>P_d</math>:</b><br>0.92             |
| <b>Bevel:</b><br>Protective as needed                          |

Regulatory Compliance

|                                                            |
|------------------------------------------------------------|
| <b>RoHS 2015:</b><br><a href="#">Compliant</a>             |
| <b>Certificate of Conformance:</b><br><a href="#">View</a> |